



# NEMA 4X Gasketed Screw Cover 8X10X4 316 Stainless Steel

By Wiegmann  
Catalog # [WA081004GSCSSA](#)

NEMA 4X Gasketed Screw Cover 8X10X4 316 Stainless Steel



\*Representative Image

## Features

- 
- 
- 
- 
- 

## General

Application	Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained
Material	316 Stainless Steel
Mounting Type	Wall
Number of Doors (Fixed)	1
UPC	786725890941

## Dimensions

Actual Height	8.125 in
Actual Width	10.125 in
Cubic Capacity	320 cu.in
Depth	4 in
Height	8 in
Width	10 in

## Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12, 13

## Logistics

Carton Quantity                      1 EA

## Product Assets

- [3D Models - WA081004GSCSSA](#)
- [Catalogs - Wiegmann Stainless Steel & Aluminium](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWA081004GSCSS-S](#)
- [Engineering Drawing - HWDWA081004GSCSSA-S](#)
- [Sales Drawings - HWDWA081004GSCSSA-S](#)
- [Sales Drawings - HWDWA081004GSCSS-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - NEMA 4X Stainless Steel Screw Cover Enclosures](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WIEG-WA081004GSCSSA-SPEC-EN | REV 6/2024