



NEMA 4X Gasketed Screw Cover 16X16X8 304 Stainless Steel

By Wiegmann
Catalog # [WA161608GSCSS](#)

NEMA 4X Gasketed Screw Cover 16X16X8 304 Stainless Steel



*Representative Image

Features

- Bodies and covers are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Cover contains a closed cell oil resistant neoprene gasket
- Ground stud is located on the inside of the cover
- No mounting provisions are provided

General

Application	Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained
Material	304 Stainless Steel
Mounting Type	Wall
Number of Doors (Fixed)	1
UPC	786725880652

Dimensions

Actual Height	16.125 in
Actual Width	16.125 in
Cubic Capacity	2048 cu.in
Depth	8 in
Height	16 in
Width	16 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12, 13

Logistics

Carton Quantity 1

Product Assets

- [Catalogs - Wiegmann Stainless Steel & Aluminium](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - WA161608GSCSS-MOD](#)
- [Engineering Drawing - MOD Center Drawings Instructions](#)
- [Engineering Drawing - HWDWA161608GSCSS-S](#)
- [Sales Drawings - HWDWA161608GSCSS-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - NEMA 4X Stainless Steel Screw Cover Enclosures](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-WA161608GSCSS-SPEC-EN | REV 6/2024