

# NEMA 4X Gasketed Screw Cover 16X16X8 316 Stainless Steel

By Wiegmann  
Catalog # [WA161608GSCSSA](#)

NEMA 4X Gasketed Screw Cover 16X16X8 316 Stainless Steel



\*Representative Image

## Features

- Bodies and covers are fabricated from 316 stainless steel
- Seams are continuously welded and ground smooth
- Cover contains a closed cell oil resistant neoprene gasket
- Ground stud is located on the inside of the cover
- No mounting provisions are provided

## Application

Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.

## General

Catalog Number	WA161608GSCSSA
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained
Material	316 Stainless Steel
Mounting Type	Wall
Number of Doors (Fixed)	1
UPC	786725891030

## Dimensions

Actual Height	16.125 in
---------------	-----------

Actual Width	16.125 in
Cubic Capacity	2048 cu.in
Depth	8 in
Height	16 in
Width	16 in

## Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12, 13

## Logistics

Carton Quantity	1 EA
-----------------	------

## Product Assets

- [3D Models - WA161608GSCSSA](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWA161608GSCSS-S](#)
- [Engineering Drawing - HWDWA161608GSCSSA-S](#)
- [Sales Drawings - HWDWA161608GSCSS-S](#)
- [Sales Drawings - HWDWA161608GSCSSA-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - NEMA 4X Stainless Steel Screw Cover Enclosures](#)
- [Specifications - WA161608GSCSSA](#)
- [Terms and Conditions - HCC Terms & Conditions](#)