

NEMA 4X Gasketed Screw Cover 24X24X6 316 Stainless Steel

By Wiegmann
Catalog # [WA242406GSCSSA](#)

NEMA 4X Gasketed Screw Cover 24X24X6 316 Stainless Steel



*Representative Image

Features

- Bodies and covers are fabricated from 316 stainless steel
- Seams are continuously welded and ground smooth
- Cover contains a closed cell oil resistant neoprene gasket
- Ground stud is located on the inside of the cover
- No mounting provisions are provided

Application

Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.

General

Catalog Number	WA242406GSCSSA
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained
Material	316 Stainless Steel
Mounting Type	Wall
Number of Doors (Fixed)	1
UPC	786725891078

Dimensions

Actual Height	24.125 in
Actual Width	24.125 in

Cubic Capacity	3456 cu.in
Depth	6 in
Height	24 in
Width	24 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus
Nema Rating	4, 4X, 12, 13

Logistics

Carton Quantity	1 EA
-----------------	------

Product Assets

[3D Models - WA242406GSCSSA](#)
[Catalogs - Section E Stainless Steel & Aluminium](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - HWDWA242406GSCSS-S](#)
[Engineering Drawing - HWDWA242406GSCSSA-S](#)
[Sales Drawings - HWDWA242406GSCSS-S](#)
[Sales Drawings - HWDWA242406GSCSSA-S](#)
[SDS - HCC SDS](#)
[Sell Sheets - NEMA 4X Stainless Steel Screw Cover Enclosures](#)
[Specifications - WA242406GSCSSA](#)
[Terms and Conditions - HCC Terms & Conditions](#)