



NEMA 4X Gasketed Screw Cover 36X36X12 316 Stainless Steel

By Wiegmann
Catalog # [WA363612GSCSSA](#)

NEMA 4X Gasketed Screw Cover 36X36X12 316 Stainless Steel



*Representative Image

Features

- Bodies and covers are fabricated from 316 stainless steel
- Seams are continuously welded and ground smooth
- Cover contains a closed cell oil resistant neoprene gasket
- Ground stud is located on the inside of the cover
- No mounting provisions are provided

General

Application	Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained
Material	316 Stainless Steel
Mounting Type	Wall
Number of Doors (Fixed)	1
UPC	786725891108

Dimensions

Actual Height	36.25 in
Actual Width	36.25 in
Cubic Capacity	15552 cu.in
Depth	12 in
Height	36 in
Width	36 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12, 13

Logistics

Carton Quantity 1 EA

Product Assets

- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWA363612GSCSS-S](#)
- [Sales Drawings - HWDWA363612GSCSS-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - NEMA 4X Stainless Steel Screw Cover Enclosures](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-WA363612GSCSSA-SPEC-EN | REV 6/2024