



NEMA 4X Deep Hinged Blank Cover 14.8 X 9.5 X 2.8, 304 Stainless Steel

By Wiegmann
Catalog # [WADW150902BCSS](#)

NEMA 4X Deep Hinged Blank Cover 14.8X9.5X2.8 304 Stainless Steel



*Representative Image

Features

- Quarter-turn style latching for wasy access
- Poured in place gasket
- Removable concealed hinge
- Drill template included for ease of mounting and guaranteed alignment

General

Accessory Type	Window/Door Kit
Color	Stainless Steel
EU RoHS Indicator	No
Finish Type	Stainless Steel
Latches Type	Quarter Turn Latch
Material	304 Stainless Steel
Type	Accessory
UPC	786725885503

Dimensions

Actual Depth	2.75 in
Actual Height	14.75 in
Actual Width	9.5 in
Depth	2 in
Height	15 in
Width	9 in

Certifications and Compliance

Certified Listed	UL Recognized 508A
Nema Rating	4X

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - WADW150902BCSS](#)
- [Catalogs - Wiegmann Accessories](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWADW150902BCSS-S](#)
- [Sales Drawings - HWDWADW150902BCSS-S](#)
- [SDS - HCC_SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-WADW150902BCSS-SPEC-EN | REV 1/2024