



NEMA 4 Deep Hinged Blank Cover 22.8 X 26.3 X 2.8, Carbon Steel-Gray

By Wiegmann
Catalog # [WADW232602BC](#)

NEMA 4 Deep Hinged Blank Cover 22.8X26.3X2.8 Carbon Steel-Gray



*Representative Image

Features

- Quarter-turn style latching for wasy access
- Poured in place gasket
- Removable concealed hinge
- Drill template included for ease of mounting and guaranteed alignment

General

Accessory Type	Window/Door Kit
Color	Gray
EU RoHS Indicator	No
Finish Type	Polyester Powder
Latches Type	Quarter Turn Latch
Material	Carbon Steel
Type	Accessory
UPC	786725885473

Dimensions

Actual Depth	2.75 in
Actual Height	22.75 in
Actual Width	26.25 in
Depth	2 in
Height	23 in
Width	26 in

Certifications And Compliance

Certified Listed	UL Recognized 508A
Nema Rating	4, 12

Logistics

Carton Quantity 1

Product Assets

- [3D Models - WADW232602BC](#)
- [Catalogs - Wiegmann Accessories](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWADW232602BC-S](#)
- [Sales Drawings - HWDWADW232602BC-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-WADW232602BC-SPEC-EN | REV 6/2024