



## LED Steady Signal Light 120-240VAC Red

By Wiegmann  
Catalog # [WLSG25R](#)

LED Steady Signal Light 120-240VAC Red



\*Representative Image

### Features

- 50,000 hour life expectancy
- Inverted cone design to provide full 360 degree coverage for more light projection
- Flash rate is approximately 7 micro flashes per second
- Includes gasket and locknut

### General

|                   |              |
|-------------------|--------------|
| Color             | Red          |
| EU RoHS Indicator | No           |
| Type              | Signal Light |
| UPC               | 786725871261 |

### Dimensions

|        |         |
|--------|---------|
| Height | 3.38 in |
| Weight | 1.25 lb |
| Width  | 2.89 in |

### Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

### Product Assets

- [Catalogs - Wiegmann Accessories](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)