



LED Steady Signal Light 12-80V Clear

By Wiegmann
Catalog # [WLSG26C](#)

LED Steady Signal Light 12-80V Clear



*Representative Image

Features

- 50,000 hour life expectancy
- Inverted cone design to provide full 360 degree coverage for more light projection
- Flash rate is approximately 7 micro flashes per second
- Includes gasket and locknut

General

Color	Clear
EU RoHS Indicator	No
Type	Signal Light
UPC	786725871346

Dimensions

Height	3.38 in
Weight	1.25 lb
Width	2.89 in

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Catalogs - Wiegmann Accessories](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-WLSG26C-SPEC-EN | REV 1/2024