



NEMA 4 1-Door Freestanding Enclosure with KwikHinge™ and 3-Point Handle 72X36X36 Carbon Steel

By Wiegmann
Catalog # [WRD723636FS4](#)



*Representative Image

NEMA 4 1-Door Freestanding Enclosure with KwikHinge™ and 3-Point Handle 72X36X36 Carbon Steel

Features

- Body and door are fabricated from carbon steel
- Entire WRD series features our KwikHinge™ technology which allows enclosure doors to be quickly and easily removed by simply sliding the Heavy-Duty, 316 Stainless Steel, hinge pin
- Seams are continuously welded and ground smooth and the doors are sealed with a poured in place gaskets
- This enclosure includes 3-point keylocking/padlocking combo handle

General

Catalog Number	WRD723636FS4
Color	Gray
Cover Type	KwikHinge™
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Series	KwikHinge™
Type	Enclosure
UPC	786725880485

Dimensions

Actual Depth	36.13 in
Actual Height	72.13 in
Actual Width	36.13 in
Cubic Capacity	93312 cu.in

Depth	36 in
Height	72 in
Weight	465 lb
Width	36 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	cULus
Nema Rating	3R, 4, 12 and IP66

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - WRD723636FS4](#)
- [Brochures - KwikHinge™ Series Enclosures Featuring Removable Hinge Pins](#)
- [Brochures - NEMA 4 & IP66 Removable Hinge Single Door & Double Door Freestanding](#)
- [Catalogs - Section D NEMA 4 Enclosures](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWRD723636FS4-S](#)
- [Sales Drawings - HWDWRD723636FS4-S](#)
- [SDS - HCC SDS](#)
- [Specifications - WRD723636FS4](#)
- [Terms and Conditions - HCC Terms & Conditions](#)