



NEMA 4 1-Door Freestanding Enclosure with KwikHinge™ and 3-Point Handle 90X24X20 Carbon Steel

By Wiegmann
Catalog # [WRD902420FS4](#)

NEMA 4 1-Door Freestanding Enclosure with KwikHinge™ and 3-Point Handle 90X24X20 Carbon Steel



*Representative Image

Features

- Body and door are fabricated from carbon steel
- Entire WRD series features our KwikHinge™ technology which allows enclosure doors to be quickly and easily removed by simply sliding the Heavy-Duty, 316 Stainless Steel, hinge pin
- Seams are continuously welded and ground smooth and the doors are sealed with a poured in place gaskets
- This enclosure includes 3-point keylocking/padlocking combo handle

General

Color	Gray
Cover Type	KwikHinge™
Finish Type	Polyester Powder
Material	Carbon Steel
Mounting Type	Freestanding
Number of Doors (Fixed)	1
Series	KwikHinge™
Type	Enclosure
UPC	786725880409

Dimensions

Actual Depth	20.13 in
Actual Height	90.13 in
Actual Width	24.13 in
Cubic Capacity	43200 cu.in
Depth	20 in
Height	90 in
Weight	315 lb
Width	24 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	3R, 4, 12 and IP66

Logistics

Carton Quantity 1

Product Assets

- [3D Models - WRD902420FS4](#)
- [Brochures - KwikHinge™ Series Enclosures Featuring Removable Hinge Pins](#)
- [Brochures - NEMA 4 & IP66 Removable Hinge Single Door & Double Door Freestanding](#)
- [Catalogs - Wiegmann NEMA 4 Enclosures](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWRD902420FS4-S](#)
- [Sales Drawings - HWDWRD902420FS4-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-WRD902420FS4-SPEC-EN | REV 6/2024