



N12 JIC Continuous Hinge 12X10X8 Carbon Steel - Gray

By Wiegmann
Catalog # [B121008CH](#)

N12 JIC Continuous Hinge 12X10X8 Carbon Steel - Gray



*Representative Image

Features

- Bodies fabricated from 14 gauge and doors fabricated from 16 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Lids are sealed with closed cell oil resistant neoprene gasket. External mounting plates, top and bottom of enclosure. Weldnuts are provided for mounting optional panels securely. External screw clamps are quick and easy to operate. Standard continuous hinge. Grounding provisions provided.

Application

Intended for use as electrical junction boxes, terminal wiring boxes, and instrument housings. Hinged door provides convenient access. Designed to provide protection from dust, dirt, oil, and water.

General

Catalog Number	B121008CH
Construction	Continuously Welded Seams
Cover Type	Hinged Cover
EU RoHS Indicator	Yes
Finish Type	Textured
Latches Type	Clamps
Material	Carbon Steel
Mounting Type	External Mounting Plates
Type	Enclosure
UPC	786725332021

Dimensions

Depth	8 in
Height	12 in
Weight	16 lb
Width	10 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	12
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - B121008CH](#)
- [Brochures - Modify Enclosures and Panels in 3-5 days](#)
- [Catalogs - Section C NEMA 12 Enclosures](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - B121008CH-MOD](#)
- [Engineering Drawing - MOD Center Drawings Instructions](#)
- [Engineering Drawing - HWDB121008CH-S](#)
- [Sales Drawings - HWDB121008CH-S](#)
- [SDS - HCC SDS](#)
- [Specifications - B121008CH Specification Sheet English](#)
- [Specifications - B121008CH Specification Sheet French](#)
- [Specifications - B121008CH](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand