



NEMA 4X JIC Continuous Hinge Link Lock With Window 10X8X5 Fiberglass-Opaque

By Wiegmann
Catalog Number [HW-J100805CHTLW](#)

NEMA 4X JIC Continuous Hinge Link Lock With Window
10X8X5 Fiberglass-Opaque.



*Representative Image

Features

- Constructed of molded fiberglass
- Windowed cover with continuous hinge and twist-lock latches
- Poured seamless gasket provides a water-tight and dust-tight seal
- Mounting provisions are provided

General

Color	Gray
Cover Type	Hinged Cover with Window
EU RoHS Indicator	No
Material	Fiberglass
Mounting Type	Wall Mount
Series	JIC
Type	Enclosure
UPC	786725857357

Dimensions

Actual Depth	5.06 in
Actual Height	11.62 in
Actual Width	9.37 in
Cubic Capacity	400 cu.in
Depth	5 in
Height	10 in
Weight	5 lb
Width	8 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - HW-J100805CHTLW](#)
- [Engineering Drawing - HWDHW-J100805CHTLW-S](#)
- [SDS - HCC_SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.