

N4 Single Door Wall-Mount 60X36X10 Carbon Steel - Gray

By Wiegmann
Catalog # [N4603610](#)

N4 Single Door Wall-Mount 60X36X10 Carbon Steel - Gray

Features

- Intended for use in housing electrical and electronic controls, instruments, components and associated wiring, these enclosures incorporate hinged doors which provide convenient access
- Designed for indoor or outdoor use in protecting components from dust, dirt,oil and those directed water.

Application

Intended for use in housing electrical and electronic controls, instruments, components, and associated wiring, these enclosures incorporate hinged doors which provide convenient access. Designed for indoor or outdoor use in protecting components from dus

General

Catalog Number	N4603610
Construction	Continuously Welded Seams
Cover Type	Door
EU RoHS Indicator	Yes
Finish Type	Textured
Latches Type	Clamps;Hasp and Staple
Material	Carbon Steel
Mounting Type	External Mounting Feet
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725372652

Dimensions



*Representative Image

Cubic Capacity	129600 cu.in
Depth	60 in
Height	60 in
Weight	166 lb
Width	36 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none"> cULus IEC
Nema Rating	4
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - N4603610](#)
- [Brochures - Modify Enclosures and Panels in 3-5 days](#)
- [Catalogs - Section D NEMA 4 Enclosures](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDN4603610-S](#)
- [Sales Drawings - HWDN4603610-S](#)
- [SDS - HCC SDS](#)
- [Specifications - N4603610 Specification Sheet English](#)
- [Specifications - N4603610 Specification Sheet French](#)
- [Specifications - N4603610](#)
- [Terms and Conditions - HCC Terms & Conditions](#)