

N1 Screw-Cover Wireway

2.5X2.5X12 Carbon Steel - Galvanized

By Wiegmann
Catalog # [S2212G](#)



N1 Screw-Cover Wireway 2.5X2.5X12 Carbon Steel - Galvanized

*Representative Image

Features

- Bodies and covers are fabricated from 16 gauge pre-galvanized steel. S Series screw cover design covers held firmly in place with captivated screw fasteners. Straight sections with knockouts are provided on side walls on wireways.

Application

Designed to protect electrical wiring in applications where dirt, dust, oil, and water are not serious problems. All sections are open on one side so wires and cable can be laid in along an entire wireway run.

General

Catalog Number	S2212G
Cover Type	Screw Cover
EU RoHS Indicator	Yes
Enclosure Type	Nema 1 Type Enclosure
Finish Type	Galvanized
Knockouts	Yes
Material	Carbon Steel
Type	Wireway
UPC	786725851454

Dimensions

Actual Height	2.5 in
---------------	--------

Actual Length	12 in
Actual Width	2.5 in
Depth	12 in
Height	3 in
Weight	9 lb
Width	3 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	1
UL Listed	Yes

Logistics

Carton Quantity	4
-----------------	---

Product Assets

- [3D Models - S2212G](#)
- [Catalogs - Section H Wireways & Fittings](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDS2212G-S](#)
- [Sales Drawings - HWDS2212G-S](#)
- [SDS - HCC SDS](#)
- [Specifications - S2212G Specification Sheet English](#)
- [Specifications - S2212G Specification Sheet French](#)
- [Specifications - S2212G](#)
- [Terms and Conditions - HCC Terms & Conditions](#)