



N4X Single Door Wall-Mount Clamp 20X16X10 316 Stainless Steel

By Wiegmann
Catalog # [SSN4201610A](#)

N4X Single Door Wall-Mount Clamp 20X16X10 316 Stainless Steel

Features

- Provides unmatched protection for housing electrical components in highly corrosive environments
- This enclosure is used in indoor and outdoor settings that are frequently wet or have constant exposure to water, other liquids or contaminants
- A wide variety of type 316 stainless steel enclosures are available specifically for applications in food processing plants and offshore oil exploration.

Application

Provides unmatched protection for housing electrical components in highly corrosive environments. This enclosure is used in indoor and outdoor settings that are frequently wet or have constant exposure to water, other liquids, or containments.

General

Catalog Number	SSN4201610A
Construction	Continuously Welded Seams
EU RoHS Indicator	No
Knockouts	No
Latches Type	Clamps
Material	Stainless Steel
Mounting Type	External Mounting Feet
Number of Doors (Fixed)	1
Series	SSN4-A
Type	Enclosure
UPC	786725848089

Dimensions



*Representative Image

Actual Depth	22.5 in
Actual Width	20.5 in
Cubic Capacity	5796 cu.in
Depth	23 in
Height	12 in
Weight	37 lb
Width	21 in

Certifications And Compliance

Certified Listed	<ul style="list-style-type: none">• cULus• IEC
Nema Rating	4X
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - SSN4201610A](#)
- [Brochures - Nema 4X Stainless Steel & Aluminum Enclosures](#)
- [Brochures - Modify Enclosures and Panels in 3-5 days](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDSSN4201610A-S](#)
- [Sales Drawings - HWDSSN4201610A-S](#)
- [SDS - HCC SDS](#)
- [Specifications - SSN4201610A](#)
- [Specifications - SSN4201610A Specification Sheet English](#)
- [Specifications - SSN4201610A](#)
- [Terms and Conditions - HCC Terms & Conditions](#)