

Hinged-Cover Wire Trough

2.5X2.5X36 Carbon Steel - Gray

By Wiegmann
Catalog # [T2236CH](#)

Hinged-Cover Wire Trough 2.5X2.5X36 Carbon Steel - Gray



*Representative Image

Features

- Trough and cover fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Oil resistant gasket and adhesive are provided. Trough comes complete with easy to operate external clamps and a continuous hinge. External mounting feet are provided.

Application

Designed to protect from dirt, dust, oil, and water.

General

Accessory Type	Trough
Catalog Number	T2236CH
Cover Type	Hinged Cover
EU RoHS Indicator	No
Finish Type	Polyester Powder
Knockouts	No
Material	Carbon Steel
Type	Trough
UPC	786725326310

Dimensions

Actual Height	2.5 in
Actual Length	36 in
Actual Width	2.5 in

Depth	36 in
Height	3 in
Weight	9 lb
Width	3 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, IP66
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - T2236CH](#)
- [Brochures - Modify Enclosures and Panels in 3-5 days](#)
- [Catalogs - Section H Wireways & Fittings](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDT2236CH-S](#)
- [Sales Drawings - T2236CH-S](#)
- [SDS - HCC SDS](#)
- [Specifications - T2236CH Specification Sheet English](#)
- [Specifications - T2236CH](#)
- [Specifications - T2236CH Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)