



N12 JIC Hinged Screw-Cover 8X6X4 Carbon Steel - Gray

By Wiegmann
Catalog # [WA080604GIE](#)

N12 JIC Hinged Screw-Cover 8X6X4 Carbon Steel - Gray

Features

- Fabricated from 14 gauge steel. Continuously welded seams ground smooth, less knockouts or holes. Lids are sealed with closed cell oil resistant neoprene gasket. Cover is secured by continuous hinge. Captivated door screws thread into sealed wells. No mounting feet or mounting holes are provided. Weldnuts are provided to mount optional panels. Grounding provisions provided.

Application

Designed for use as instrument housings, electrical control enclosures, terminal wiring boxes, or electrical junction boxes. Provides protection from dirt, dust, oil, and water.

General

Catalog Number	WA080604GIE
Construction	Continuously Welded Seams
Cover Type	Hinged Screw Cover
EU RoHS Indicator	No
Finish Type	Textured
Material	Carbon Steel
Mounting Type	Wall Mount
Type	Enclosure
UPC	786725442058

Dimensions



*Representative Image

Depth	4 in
Height	8 in
Weight	5.38 lb
Width	6 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	12
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - WA080604GIE](#)
- [Brochures - Modify Enclosures and Panels in 3-5 days](#)
- [Catalogs - Section C NEMA 12 Enclosures](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWA080604GIE-S](#)
- [Sales Drawings - WA080604GIE-S](#)
- [Sales Drawings - HWDWA080604GIE-S](#)
- [SDS - HCC SDS](#)
- [Specifications - WA080604GIE](#)
- [Specifications - WA080604GIE Specification Sheet English](#)
- [Specifications - WA080604GIE Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand