



NEMA 4X Gasketed Screw Cover 24X24X6 304 Stainless Steel

By Wiegmann
Catalog # [WA242406GSCSS](#)

NEMA 4X Gasketed Screw Cover 24X24X6 304 Stainless Steel.



*Representative Image

Application

Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.

General

Catalog Number	WA242406GSCSS
Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained
Material	304 Stainless Steel
Mounting Type	Wall
Number of Doors (Fixed)	1
UPC	786725883523

Dimensions

Actual Height	24.125 in
Actual Width	24.125 in
Cubic Capacity	3456 cu.in
Depth	6 in

Height	24 in
Width	24 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12, 13

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDWA242406GSCSS-S](#)
- [Engineering Drawing - MOD Center Drawings Instructions](#)
- [Engineering Drawing - WA242406GSCSS-MOD](#)
- [Sales Drawings - HWDWA242406GSCSS-S](#)
- [SDS - HCC SDS](#)
- [Sell Sheets - NEMA 4X Stainless Steel Screw Cover Enclosures](#)
- [Specifications - WA242406GSCSS Specification Sheet French](#)
- [Terms and Conditions - HCC Terms & Conditions](#)