



N412 Double Door Wall-Mount Ultimate 24X42X08 Stainless Steel

By Wiegmann
Catalog # [N412D244208SSC](#)



N412 Double Door Wall-Mount Ultimate 24X42X08 Stainless Steel

Features

- Stainless steel construction
- Continuous welded seams
- Doors sealed with poured-in-place gaskets
- Grounding studs welded to doors and body
- Collar studs for mounting optional ULTIMATE series back panels
- 3-point keylocking/padlocking handle included
- NEMA 3R, 4, 4X, 12, 13 and IP66

General

Construction	Continuously Welded Seams
Cover Type	Door
Latches Type	3-Point Handle
Material	Stainless Steel
Mounting Type	Mounting Holes
Number of Doors (Fixed)	2
Series	Ultimate
Type	Enclosure
UPC	786725890491

Dimensions

Cubic Capacity	8064 cu.in
Depth	8 in
Height	24 in
Width	42 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• cULus Listed• IEC 60529, IP66
Nema Rating	NEMA 3R;NEMA 4;NEMA 4X;NEMA 12;NEMA 13

Product Assets

- [3D Models - N412D244208SSC](#)
- [Engineering Drawing - HWDN412D244208SSC-S](#)
- [Sales Drawings - HWDN412D244208SSC-S](#)
- [SDS - HCC_SDS](#)
- [Sell Sheets - N412 ULTIMATE Stainless Steel Series Double Door Enclosure](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WIEG_N412D244208SSC_SPEC | REV 3/2023