



NEMA 4X Gasketed Screw Cover 8X8X4 304 Stainless Steel

By Wiegmann
Catalog # [WA080804GSCSS](#)

NEMA 4X Gasketed Screw Cover 8X8X4 304 Stainless Steel



*Representative Image

Features

- Bodies and covers are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Cover contains a closed cell oil resistant neoprene gasket
- Ground stud is located on the inside of the cover
- No mounting provisions are provided

Application

Designed for use as a wiring box, junction box, pull box, or terminal box with many indoor and outdoor applications where dust or moisture is a problem.

General

Construction	Continuously Welded Seams
Cover Type	Screw Cover
Finish Type	Smooth Grained
Material	304 Stainless Steel
Mounting Type	Wall
Number of Doors (Fixed)	1
UPC	786725880546

Dimensions

Actual Height	8.125 in
Actual Width	8.125 in
Cubic Capacity	256 cu.in
Depth	4 in
Height	8 in
Width	8 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12, 13

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - MOD Center Drawings Instructions](#)
- [Engineering Drawing - HWDWA080804GSCSS-S](#)
- [Engineering Drawing - WA080804GSCSS-MOD](#)
- [Sales Drawings - HWDWA080804GSCSS-S](#)
- [SDS - HCC_SDS](#)
- [Sell Sheets - NEMA 4X Stainless Steel Screw Cover Enclosures](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
WIEG_WA080804GSCSS_SPEC | REV 3/2023