Switches, Three Way 20A, 120-277V AC

Pre-Wired Hubbell-PRO Heavy Duty **Industrial Switch**

HUBBELL

Features

- Steel, zinc plated bridge is corrosion resistant
- Color Coded by Amperage makes inspection easy even when installed
- Strip gauge for accurate wiring

Ordering Information

Toggle Color Description UPC Catalog Number Toggle, Pre-wired 783585188232 1223PWGY leads

Listings

UL Listed **CSA Certified** Fed. Spec. W-S-896

Specifications

Top Material Thermoplastic, Red Base Material Thermoplastic, Black

Toggle Material Nylon Silver Alloy Contacts **Brass Terminal Screws** Zinc Plated Steel

Auto Grounding Mounting

Bridge

Ground Screw Brass (Green)

Performance

Electrical

Withstands 1500V AC minimum for 1 minute Dielectric Voltage

Max. Continuous Current 20A Max. Working Voltage 277V AC

Overload Minimum 4.8 times rated current for 100 cycles

Temperature Rise 30°C maximum at rated current

Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper


wire only

Environmental

Flammability UL 94V-2

Operating Temperature Max. continuous: 75°C; Min. continuous: -40°C without





Online Resources

Customer Use Drawing

eCatalog

Installation Instructions

