Switches, Four Way 20A, 120-277V AC

Pre-Wired Hubbell-PRO Heavy Duty Industrial Switch

HUBBELL

Features

- Steel, zinc plated bridge is corrosion resistant
- Color Coded by Amperage makes inspection easy even when installed
- Strip gauge for accurate wiring

Ordering Information

Description	Toggle Color	UPC	Catalog Number
Toggle, Pre-wired	Light Almond	783585188331	1224PWLA
leads			

Listings

UL Listed CSA Certified Fed. Spec. W-S-896

Specifications

Top Material Thermoplastic, Red
Base Material Thermoplastic, Black
Toggle Material Nylon

Contacts Silver Alloy
Terminal Screws Brass
Auto Crounding Mounting Zine Ploted Silver Alloy

Auto Grounding Mounting Zinc Plated Steel

Bridge

Ground Screw Brass (Green)

Performance

Electrical

Dielectric Voltage Withstands 1500V AC minimum for 1 minute

Max. Continuous Current 20A Max. Working Voltage 277V AC

Overload Minimum 4.8 times rated current for 100 cycles

Temperature Rise 30°C maximum at rated current

Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper

wire only


Environmental

Flammability UL 94V-2

Operating Temperature Max. continuous: 75°C; Min. continuous: -40°C without

impact





Online Resources

Customer Use Drawing

eCatalog

Installation Instructions

