# Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Hubbell-PRO Heavy Duty Hospital Grade Receptacles

# HUBBELL

## **Features**

- Triple wipe contacts
- High impact resistant decorator face
- Steel mounting strap

# **Ordering Information**

Description Device Color UPC Catalog Number Hospital grade. Style 783585196589 2182IV Line® decorator

## Listings

UL Listed to UL498 File No. E2186 Certified to CSA, C22.2, No. 42 File 285 Fed. Spec. W-C-596 **NEMA® WD-6 Compliant** 

# **Specifications**

Face Nylon PBT Base **Power Contacts Brass Ground Contacts Brass** Clamping Plate Plated steel Mounting Strap Galvalized steel Automatic Self-grounding Stainless steel Staple Mounting Screws Zinc plated steel

#### **Performance**

# **Electrical**

Certified for current interrupting at full rated current **Current Interrupting** Dielectric Voltage Withstands 2,000V minimum

#### Mechanical

**Product Identification** Ratings are a permanent part of the device **Terminal Accommodation** #12-#10 AWG stranded or solid copper wire only **Terminal Identification** Terminals identified in accordance with UL 498 and CSA

# **Environmental**

UL 94V-2 Flammability

**Operating Temperature** Maximum continuous 75°C; minimum -40°C (w/o impact)



#### Accessories

Wallplate or Weatherproof Cover StyleLine® Decorator Opening

# Resources

**Customer Use Drawing** eCatalog

