

Straight Blade Devices 15A, 125V, 2 Pole, 3 Wire Grounding Illuminated Plug

HUBBELL

Features

- Durable Polycarbonate and Nylon
- 360 Degree LED Visibility Around Body
- Accepts Both Round and Flat Cable
- Elastomeric dust seal prevents dust, moisture, and contaminants from entering the wiring chamber



Ordering Information

Description	UPC	Catalog Number
PLUG, 15A 125V, 5-15P, ILLUMINATED	783585531267	515LP

Listings

UL498 File No. E1381
Certified to CSA C22.2 No. 42
Fed. Spec. W-C-596

Specifications

Housing/Cord Clamp	Thermoplastic
Blade Holder	Thermoplastic
Terminal Retainer	Thermoplastic
Blades	Brass
Terminal Screws	Brass
Terminal Clamp	Brass
Assembly Screws	Steel

Performance

Electrical	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

Mechanical	
Product Identification	Ratings are a permanent part of the device
Terminal Identification	Terminals identified in accordance with UL 498 and CSA C22.2 No. 42
Terminal Accommodation	14-10 AWG stranded copper wire only

Environmental	
Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; Minimum -40°C (w/o impact)

Online Resources

Sales Drawing
Installation Manual

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

