

# Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Illuminated Connector

# HUBBELL

## Features

- Durable Polycarbonate and Nylon
- 360 Degree LED Visibility Around Body
- Accepts Both Round and Flat Cable
- Elastomeric dust seal prevents dust, moisture, and contaminants from entering the wiring chamber



## Ordering Information

Description CONN, 20A 125V, 5-20R, ILLUMINATED	UPC 783585531298	Catalog Number <b>520LC</b>
--	---------------------	--------------------------------

## Listings

UL498 File No. E1381  
Certified to CSA C22.2 No. 42  
Fed. Spec. W-C-596

## Specifications

Housing/Cord Clamp	Thermoplastic
Contact Holder	Thermoplastic
Terminal Retainer	Thermoplastic
Contacts	Brass
Terminal Screws	Brass
Terminal Clamp	Brass
Assembly Screws	Steel

## Performance

<b>Electrical</b>	
Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

<b>Mechanical</b>	
Product Identification	Ratings are a permanent part of the device
Terminal Identification	Terminals identified in accordance with UL 498 and CSA C22.2 No. 42
Terminal Accommodation	14-10 AWG stranded copper wire only

<b>Environmental</b>	
Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; Minimum -40°C (w/o impact)

## Online Resources

Sales Drawing  
Installation Manual

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

