

Straight Blade Devices

20A, 125V, 2 Pole, 3 Wire Grounding

Hubbell-Pro™ Extra Heavy Duty Duplex Receptacles

Features

- Slender/compact design
- Smooth Face
- Triple wipe contacts

Ordering Information

| Description | Device Color | UPC | Catalog Number |
|---------------------|--------------|---------------|----------------|
| Back and side wired | Light Almond | 7783585530833 | 5352LA |

Listings

UL Listed to UL498 File No. E2186
Certified to CSA 22.2, No. 42
Fed. Spec. W-C-596
NEMA® WD-6 Compliant

Specifications

| | |
|---------------------------------|-------------------------|
| Material | Thermoplastic/Composite |
| Contacts | Brass |
| Mounting Strap | Galvanized steel |
| Automatic Self-grounding Staple | Stainless steel |
| Mounting Screws | Zinc plated steel |

Performance

| | |
|-------------------------|--|
| Electrical | |
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |
| Mechanical | |
| Product Identification | Ratings are a permanent part of the device |
| Terminal Accommodation | #12-#10 AWG copper stranded or solid conductor only |
| Terminal Identification | Terminal wire leads identified in accordance with UL 498 |
| Environmental | |
| Flammability | UL 94 V-2 |
| Operating Temperatures | Maximum continuous 75°C; minimum -40°C (w/o impact) |

HUBBELL



20A 125V
NEMA 5-20R
UL CSA
1 HP



Accessories

| | |
|---------------------------------|----------------|
| Wallplate or Weatherproof Cover | Duplex Opening |
|---------------------------------|----------------|

