# Straight Blade Devices 20A, 125V, 2 Pole, 3 Wire Grounding Hubbell-Pro™ Heavy Duty Duplex Receptacles

## **Features**

- · Easy access split circuit tab
- Finder Groove Face
- · Triple wipe contacts
- Wrap-around galvanized steel strap

#### **Ordering Information**

Description Back and side wired	Device Color Gray	UPC	Catalog Number
		783585530970	5362AG

#### Listings

UL File No. E2186 Certified to CSA 22.2, No. 42 File 285 Fed. Spec. W-C-596 NEMA® WD-6 Compliant

#### **Specifications**

Material Thermoplastic/Composite

Contacts **Brass** 

Mounting Strap Galvanized steel Automatic Self-grounding Stainless steel

Staple

Mounting Screws Zinc plated steel

### **Performance**

**Electrical** 

**Current Interrupting** Certified for current interrupting at full rated current Dielectric Voltage

Withstands 2,000V minimum

Mechanical

**Product Identification** Ratings are a permanent part of the device

Terminal Accommodation #12-#10 AWG copper stranded or solid conductor only Terminal Identification

Terminal wire leads identified in accordance with UL 498

Environmental

UL 94 V-2 Flammability

**Operating Temperatures** Maximum continuous 75°C; minimum -40°C (w/o impact)



#### **Accessories**

Wallplate or Weatherproof Cover Duplex Opening

#### Resources

**Customer Use Drawing** eCatalog

