

Straight Blade Devices  
15A, 125V, 2 Pole, 3 Wire Grounding  
Hubbell-PRO Heavy Duty Hospital Grade  
Receptacles

HUBBELL

Features

- Triple wipe contacts
- High impact resistant face with circuit I.D. marking area
- Steel mounting strap

Ordering Information

| Description                                      | Device Color | UPC          | Catalog Number |
|--------------------------------------------------|--------------|--------------|----------------|
| Hospital grade, smooth face, back and side wired | Red          | 783585197487 | 8200RED        |

Listings

UL Listed to UL498 File No. E2186  
Certified to CSA, C22.2, No. 42 File 285  
Fed. Spec. W-C-596  
NEMA® WD-6 Compliant

Specifications

|                                 |                   |
|---------------------------------|-------------------|
| Face                            | Nylon             |
| Base                            | PBT               |
| Power Contacts                  | Brass             |
| Ground Contacts                 | Brass             |
| Clamping Plate                  | Plated steel      |
| Mounting Strap                  | Galvalized steel  |
| Automatic Self-grounding Staple | Stainless steel   |
| Mounting Screws                 | Zinc plated steel |

Performance

|                         |                                                          |
|-------------------------|----------------------------------------------------------|
| <b>Electrical</b>       |                                                          |
| Current Interrupting    | Certified for current interrupting at full rated current |
| Dielectric Voltage      | Withstands 2,000V minimum                                |
| <b>Mechanical</b>       |                                                          |
| Product Identification  | Ratings are a permanent part of the device               |
| Terminal Accommodation  | #14-#10 AWG copper stranded or solid conductor only      |
| Terminal Identification | Terminals identified in accordance with UL 498 and CSA   |
| <b>Environmental</b>    |                                                          |
| Flammability            | UL 94V-2                                                 |
| Operating Temperature   | Maximum continuous 75°C; minimum -40°C (w/o impact)      |



Accessories

Wallplate or Weatherproof Cover Duplex Opening

Resources

[eCatalog](#)

