

Straight Blade Devices

15A 125V, 2-Pole 3-Wire, 5-15R

EdgeConnect™ Commercial Specification Grade Duplex Receptacle

HUBBELL

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Triple and Double Wipe Contacts
- Easy access split circuit tab

Ordering Information

| Description | Device Color | UPC Number | Catalog Number |
|-------------------------|--------------|-------------|----------------|
| Smooth Face, Back Wired | Brown | 78358572768 | BR15ST |

Listings

UL Listed to UL498 File No. E2186
Certified to CSA 22.2, No. 42 File 285
NEMA® WD-6 Compliant

Specifications

| | |
|-----------------|------------------|
| Face | Polycarbonate |
| Base | Polycarbonate |
| Mounting Strap | Galvanized Steel |
| Ground Contact | Copper Alloy |
| Mounting Screws | Plated Steel |

Performance

Electrical

| | |
|----------------------|--|
| Current Interrupting | Certified for current interrupting at full rated current |
| Dielectric Voltage | Withstands 2,000V minimum |

Mechanical

| | |
|-------------------------|---|
| Product Identification | Ratings are a permanent part of the device |
| Terminal Accommodation | #14 (Solid and Stranded) - #10 (Stranded) Copper Wire Only, Consult Factory for #10 Applications |
| Terminal Identification | Terminals Identified in Accordance with UL 498 and CSA |

Environmental

| | |
|------------------------|---|
| Flammability | UL 94 V-2 |
| Operating Temperatures | Maximum continuous 75°C; minimum -40°C (w/o impact) |



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

