**Hubbell-PRO**


**100/125 A, 380-415 VAC, 3-POLE, 4-WIRE**

# Watertight Connector Body

## Features

- IP67 environmental ratings
- Impact and corrosion resistant insulated non-metallic housing
- Sequential contact engagement to prevent a momentary over-voltage
- External strain relief
- Glandless water ingress protection






## Ordering Information

| Description | Heavy Duty Products, IEC Pin and Sleeve<br>Color | UPC<br>783585676265 | Catalog Number<br>**C4100C6WA** |
|---|---|---|---|

## Listings

All constructions are UL Listed & cUL Listed
FileE14633
UL1686 Standard for Pin & Sleeve Configurations
VDE, CE

## Specifications

| | |
|---|---|
| Application | High Ampacity Connections |
| Connection | Pressure Screw Terminal |
| Wire Size | #4AWG to #1AWG |
| Material | PBT |
| Mounting | Cord Mounted |

## Performance

| | |
|---|---|
| **Electrical** | |
| Dielectric Voltage | Withstand 3000V AC |
| Max. Working Voltage | 600V AC RMS |
| **Mechanical** | |
| Impact Resistance | Per CSA C22.2 No. 182.1 / UL1682 |
| Product Identification | Identification and ratings are marked on device housing |
| Terminal Identification | Terminals identified in accordance with North American and IEC conventions |
| **Environmental** | |
| Flammability | HB |
| Ingress Protection | IP67 |
| Moisture Resistance | IEC 60309-1 |
| Temperature Rating | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |

## Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)



Wiring Device-Kellems