

Hubbell-PRO

30 A, 277/480 VAC, 4-POLE, 5-WIRE

Watertight Receptacle



- Features
- IP67 environmental ratings
 - Impact and corrosion resistant insulated non-metallic housing
 - Sequential contact engagement to prevent a momentary over-voltage
 - UL approved screwless terminations
 - Color coded housings provide quick identification of mating devices

Ordering Information

	Heavy Duty Products, IEC Pin and Sleeve	UPC	Catalog Number
Description	Color	783585675053	C530R7WA

Listings


All constructions are UL Listed & cUL Listed
FileE14632
UL1686 Standard for Pin & Sleeve Configurations
CE

Specifications

Application	High Ampacity Connections
Connection	Screwless Spring
Wire Size	#10AWG to #8AWG
Material	PBT
Mounting	Screw Mount

Performance

Electrical	
Dielectric Voltage	Withstand 3000V AC
Max. Working Voltage	600V AC RMS
Mechanical	
Impact Resistance	Per CSA C22.2 No. 182.1 / UL1682
Product Identification	Identification and ratings are marked on device housing
Terminal Identification	Terminals identified in accordance with North American and IEC conventions
Environmental	
Flammability	HB
Ingress Protection	IP67
Moisture Resistance	IEC 60309-1
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.



Complementary Products

Complementary Products	Adapter Plate, Back Box
------------------------	-------------------------

Online Resources

- Customer Sales Drawings
- eCatalog
- Installation Instructions

