

## Floor Boxes

### SystemOne ETERNAL™ Series Concrete Floorboxes

## 2-Gang Recessed

# HUBBELL

### Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- Stamped steel construction, exterior coated with fusion bonded epoxy paint for on grade use, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates

### Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Round	On/ Above Grade	783585695198	CFB2G25RCRE

### Listings

cULus Listed  
UL 514A Listed

### Specifications

Box Material	16 gauge galvanized steel
Box Finish	Green corrosion resistant epoxy paint
Top Mounting Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(2) 47.5 IN <sup>3</sup> [778 CM <sup>3</sup> ]

### Performance

#### Mechanical

Depth of Pour, Minimum	3.25" (82.6)
Depth of Pour, Recommended	3.25" (82.6)
Floor Box Cover Series	CFBS1R6xx
Floor Box Height	3.25"[82.6mm]
Floor Box Length	16.27" [413.3mm]
Floor Box Width	7.32" [185.9mm]
Trade Size Knock-Outs: Bottom	(4) ½", ¾", 1", 1¼"
Trade Size Knock-Outs: Ends	(2) ½", ¾", 1"
Trade Size Knock-Outs: Sides	(4) ½", ¾", 1"



### Related Products

3/4" Prepour stackable ring extensions CFB6RCVRR075

3-Cubes, Single Circuit PWFBMP3R

### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

