

Floor Boxes

SystemOne ETERNAL™ Series Concrete Floorboxes

2-Gang Recessed

Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- Stamped steel construction, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates

Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Round	Above Grade	783585695181	CFB2G25RE

Listings

cULus Listed
UL 514A Listed

Specifications

Box Material	16 gauge galvanized steel
Box Finish	Natural
Top Mounting Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(2) 47.5 IN ³ [778 CM ³]

Performance

Mechanical

Depth of Pour, Minimum	3.25" (82.6)
Depth of Pour, Recommended	3.25" (82.6)
Floor Box Cover Series	CFBS1R6xx
Floor Box Height	3.25"[82.6mm]
Floor Box Length	16.27" [413.3mm]
Floor Box Width	7.32" [185.9mm]
Trade Size Knock-Outs: Bottom	(4) ½", ¾", 1", 1¼"
Trade Size Knock-Outs: Ends	(2) ½", ¾", 1"
Trade Size Knock-Outs: Sides	(4) ½", ¾", 1"

HUBBELL



Related Products

3/4" Prepour stackable ring extensions CFB6RCVRR075

3-Cubes, Single Circuit PWF6BMP3R

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

