

## Floor Boxes

### SystemOne ETERNAL™ Series Concrete Floorboxes

#### 4-Gang Recessed

# HUBBELL

#### Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- Stamped steel construction, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates

#### Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Round	Above Grade	783585695273	CFB4G25RE

#### Listings

cULus Listed  
UL 514A Listed

#### Specifications

Box Material	16 gauge galvanized steel
Box Finish	Natural
Top Mounting Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(4) 41.5 IN <sup>3</sup> [680 CM <sup>3</sup> ]

#### Performance

##### Mechanical

Depth of Pour, Minimum	3.25" (82.6)
Depth of Pour, Recommended	3.25" (82.6)
Floor Box Cover Series	CFBS1R8xx
Floor Box Height	3.25"[82.6mm]
Floor Box Length	14.57" [370.1mm]
Floor Box Width	11.20" [284.5mm]
Trade Size Knock-Outs: Bottom	(4) 1/2", 3/4", 1", 1 1/4"
Trade Size Knock-Outs: Ends	(4) 1/2", 3/4", 1"
Trade Size Knock-Outs: Sides	(4) 1/2", 3/4", 1"



#### Related Products

3/4" Prepour stackable ring extensions CFB6RCVRR075

3-Cubes, Single Circuit PWF BMP3R

#### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

