

## Floor Boxes

### SystemOne ETERNAL™ Series Concrete Floorboxes

#### 4-Gang Recessed

# HUBBELL

#### Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- External High Capacity Feed-Thru Hubs Sold Separately
- Stamped steel construction, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates



#### Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Round	Above Grade	783585695310	CFB4G30RE

#### Listings

cULus Listed  
UL 514A Listed

#### Specifications

Box Material	16 gauge galvanized steel
Box Finish	Natural
Top Mounting Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(4) 51.0 IN <sup>3</sup> [835 CM <sup>3</sup> ]

#### Performance

##### Mechanical

Depth of Pour, Minimum	3.75" (95.3)
Depth of Pour, Recommended	3.75" (95.3)
Floor Box Cover Series	CFBS1R8xx
Floor Box Height	3.75"[95.3mm]
Floor Box Length	14.57" [370.1mm]
Floor Box Width	11.33" [287.8mm]
Trade Size Knock-Outs: Bottom	(4) ½", ¾", 1", 1¼"
Trade Size Knock-Outs: Ends	(4) ½", ¾", 1", 1¼"
Trade Size Knock-Outs: Sides	(4) ¾", 1", 1¼", 2" (Field installed CFBHUB2 for 2" metallic conduit, CFBHUB200PVC for 2" PVC conduit or CFBHUB125PVC for 1¼" PVC conduit)

#### Related Products

(2) 2" PVC field installed hubs, ships with CFBHUB200PVC  
(2) 1-1/2" reducer, (2) 1-1/4" reducers,  
and (2) 1" reducers/plugs

(2) 1-1/4" PVC field installed hubs, ships CFBHUB125PVC  
with (2) 1" reducers, (2) 3/4" reducers,  
AND (2) 1/2" reducer/plugs

2" threaded zinc hub CFBHUB2

3/4" Prepour stackable ring extensions CFB8RCVRR075

3-Cubes, Single Circuit PWF BMP3R

#### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

