

Floor Boxes

SystemOne Recessed 6 Gang Floor Box

For Use In Concrete Floors

Features

- Designed for applications requiring up to 2 in. conduits (with use of CFBHUB2 purchased separately)
- Stamped steel construction, exterior coated with fusion bonded epoxy paint for on grade use
- Pre and post pour adjustment
- Patent pending, labor saving, easy mount device plates
- Round covers

Ordering Information

- Adjustable collar for up to 1/4 in. post pour adjustment
- 6 inch solid conductor ground pigtail in each gang

Catalog Number CFB6G30RCR	UPC Number 783585527512	Cover Series CFBS1R8xx	Box Type On Grade
Device Volume 33 cu in.	Depth Behind Mounting Plate 2 1/2 in.	Min. Pour Depth 3 3/4 in.	

Specifications

Box Material	16 gauge galvanized steel
Access Cover Material (ordered separately)	Die cast aluminum


Required

- Cover
- Surface Style Rectangular Covers (for use with carpet, tile, VCT and other engineered floors) [Click here](#)

Accessories

2 in. threaded zinc hub	CFBHUB2
Replacement knock-out plate with epoxy coating	CFBKOPATECR
Replacement wire-way, used to pass wires from one compartment to the other	CFB46WW
Finished floor height adjustment ring - increase post pour adjustment 0 - 1/4 in.	CFB6RCVRR1
Finished floor height adjustment ring - increase post pour adjustment 1/4 - 1/2 in.	CFB8RCVRR2
Finished floor height adjustment ring - increase post pour adjustment 1/2 - 3/4 in.	CFB8RCVRR3

HUBBELL



Online Resources

Customer Use Drawing  
eCatalog  
Installation Instructions