

Load:Logic®
Control Panels
Dimming Switches



Features

- Provide a variety of control options for up to 4 buttons in a single-gang configuration.
- Function specific button caps supplied with units
- Connect to dimming card using UTP RJ45 patchcords



Ordering Information

Description	UPC Number	Catalog Number
Load Control Panel low voltage dimming switch, 4 button, IV	78358542741	CPSD4I

Complementary Products

Wallplate	NPS26I
Wallplate, Decorator Opening, Snap-on	NPS26I
Wallplate, Decorator Opening	NP26I
Wallplate, Decorator Opening, Stainless Steel	SS26

Specifications

Housing	Rugged, high-impact, injection-molded plastic
Dimensions	4.3" L x 1.13" W x 1.13" D

Online Resources

eCatalog

Performance

Electrical	
Power Requirements	Per switch: 10mA @ 30VDC Max
Environmental	
Operating Location	Indoor Use Only
Operating Temperature	Operating temperature: 32°to 122°F (0° to 50°C) Relative humidity (non-condensing): 10% to 90%

