

Load:Logic®
Control Panels
Dimming Switches

HUBBELL

Features

- Provide a variety of control options for up to 4 buttons in a single-gang configuration.
- Function specific button caps supplied with units
- Connect to dimming card using UTP RJ45 patchcords

Complementary Products

Wallplate	NPS26W
Wallplate, Decorator Opening, Snap-on	NPS26W
Wallplate, Decorator Opening	NP26W
Wallplate, Decorator Opening, Stainless Steel	SS26

Online Resources

eCatalog

Ordering Information

Description	UPC Number	Catalog Number
Load Control Panel low voltage dimming switch, 6 button, WH	78358545412	CPSD6W

Specifications

Housing	Rugged, high-impact, injection-molded plastic
Dimensions	4.3" L x 1.13" W x 1.13" D

Performance

Electrical	
Power Requirements	Per switch: 10mA @ 30VDC Max
Environmental	
Operating Location	Indoor Use Only
Operating Temperature	Operating temperature: 32° to 122°F (0° to 50°C) Relative humidity (non-condensing): 10% to 90%

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

