Switches, Three Way 15A, 120-277V AC

Specification Grade Commercial Switch

HUBBELL

Features

- Thread cleaning captive mounting screw
- Abuse resistant nylon toggle
- Steel, zinc plated bridge is corrosion resistant

Ordering Information

Description Toggle Color UPC Catalog Number Toggle, side wired only White 783585532202 CS315W

Listings

UL Listed CSA Certified Fed. Spec. W-S-896

Specifications

Top Material Thermoplastic, Gray
Base Material Thermoplastic, Black

Toggle Material Nylon
Contacts Silver Alloy
Terminal Screws Brass

Auto Grounding Mounting Zinc Plated Steel

Bridge

Ground Screw Brass (Green)

Performance

Electrical

Dielectric Voltage Withstands 1500V AC minimum for 1 minute

Max. Continuous Current 15A Max. Working Voltage 277V AC

Overload Minimum 4.8 times rated current for 100 cycles

Temperature Rise 30°C maximum at rated current

Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper

wire only


Environmental

Flammability UL 94V-2

Operating Temperature Max. continuous: 75°C; Min. continuous: -40°C without

impact





Online Resources

Customer Use Drawing eCatalog

