

Switches, Single Pole

15A, 120-277V AC

EdgeConnect™ Specification Grade Commercial Switch

HUBBELL

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Strip gauge for accurate wiring
- Automatic self-grounding staple

Ordering Information

Description	Color	UPC	Catalog Number
Single Pole, Toggle	White	78358596412	CSB115STW

Listings

UL Listed
CSA Certified
Fed Spec

Specifications

Material	Polycarbonate
Contacts	Silver Alloy
Mounting Bridge	Galvanized Steel

Performance

Electrical	
Dielectric Voltage	Withstands 1500V AC minimum for 1 minute
Max. Continuous Current	15A
Max. Working Voltage	277V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current

Mechanical

Terminal Accommodations	#14 AWG min. - #10 AWG max. solid and stranded copper wire only
-------------------------	---

Environmental

Flammability	UL 94V-2
Operating Temperature	Max. continuous: 75°C; Min. continuous: -40°C without impact



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

