## Switches, Single Pole 20A, 120-277V AC

### Specification Grade Commercial Switch

# HUBBELL

#### **Features**

- Thread cleaning captive mounting screw
- Abuse resistant nylon toggle
- Steel, zinc plated bridge is corrosion resistant

**Ordering Information** 

Description Toggle Color UPC Catalog Number Toggle, back and side Light Almond 783585154114 CSB120LA wired

Listings

UL Listed CSA Certified Fed. Spec. W-S-896

**Specifications** 

Top Material Thermoplastic, Gray Base Material Thermoplastic, Black

Toggle Material Nylon
Contacts Silver Alloy
Terminal Screws Brass

Auto Grounding Mounting Zinc Plated Steel

Bridge

Ground Screw Brass (Green)

#### Performance

**Electrical** 

Dielectric Voltage Withstands 1500V AC minimum for 1 minute

Max. Continuous Current 20A Max. Working Voltage 277V AC

Overload Minimum 4.8 times rated current for 100 cycles

Temperature Rise 30°C maximum at rated current

Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper

wire only


**Environmental** 

Flammability UL 94V-2

Operating Temperature Max. continuous: 75°C; Min. continuous: -40°C without

impact





#### **Online Resources**

Customer Use Drawing eCatalog

