

Switches, Three Way

20A, 120-277V AC

EdgeConnect™ Specification Grade Commercial Switch

HUBBELL

Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Strip gauge for accurate wiring
- Automatic self-grounding staple

Ordering Information

| Description | Color | UPC | Catalog Number |
|---------------|-------|-------------|----------------|
| 3-Way, Toggle | Ivory | 78358596430 | CSB320STI |

Listings

UL Listed
CSA Certified
Fed Spec

Specifications

| | |
|-----------------|------------------|
| Material | Polycarbonate |
| Contacts | Silver Alloy |
| Mounting Bridge | Galvanized Steel |

Performance

| | |
|-------------------------|--|
| Electrical | |
| Dielectric Voltage | Withstands 1500V AC minimum for 1 minute |
| Max. Continuous Current | 20A |
| Max. Working Voltage | 277V AC |
| Overload | Minimum 4.8 times rated current for 100 cycles |
| Temperature Rise | 30°C maximum at rated current |

Mechanical

| | |
|-------------------------|---|
| Terminal Accommodations | #14 AWG min. - #10 AWG max. solid and stranded copper wire only |
|-------------------------|---|

Environmental

| | |
|-----------------------|--|
| Flammability | UL 94V-2 |
| Operating Temperature | Max. continuous: 75°C; Min. continuous: -40°C without impact |



Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

