

## Straight Blade Devices

20A 125V, 2-Pole 3-Wire, 5-20R

# EdgeConnect™ Commercial Specification Grade® Style Line Duplex Receptacle

# HUBBELL

### Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Triple and Double Wipe Contacts
- Easy access split circuit tab

### Ordering Information

Description	Device Color	UPC Number	Catalog Number
Style Line® Decorator, Tamper Resistant, Back Wired	Green	78358572840	DR20STGNTR

### Listings

UL Listed to UL498 File No. E2186  
Certified to CSA 22.2, No. 42 File 285  
NEMA® WD-6 Compliant

### Specifications

Face	Polycarbonate
Base	Polycarbonate
Mounting Strap	Galvanized Steel
Ground Contact	Copper Alloy
Mounting Screws	Plated Steel

### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions



### Performance

#### Electrical

Current Interrupting	Certified for current interrupting at full rated current
Dielectric Voltage	Withstands 2,000V minimum

#### Mechanical

Product Identification	Ratings are a permanent part of the device
Terminal Accommodation	#14 (Solid and Stranded) - #10 (Stranded) Copper Wire Only, Consult Factory for #10 Applications
Terminal Identification	Terminals Identified in Accordance with UL 498 and CSA

#### Environmental

Flammability	UL 94 V-2
Operating Temperatures	Maximum continuous 75°C; minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

