Switches, Single Pole 15A, 120-277V AC

Style Line® Decorator Series Specification Grade Switch

HUBBELL

Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

Ordering Information

Description Rocker Color UPC Catalog Number Rocker, back and side Light Almond 783585151267 DS115LA wired

Listings

UL Listed CSA Certified

Specifications

Rocker Material Thermoplastic
Contacts Silver Alloy
Terminal Screws Brass
Mounting Bridge Nickel Plated Steel with Auto Ground Staple
Contacts Silver Alloy
Ground Screw Brass (Green)

Performance

Electrical

Dielectric Voltage Withstands 1500V AC minimum for 1 minute

Max. Continuous Current 15A Max. Working Voltage 277V AC

Overload Minimum 4.8 times rated current for 100 cycles

Temperature Rise 30°C maximum at rated current

Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper

wire only


Environmental

Flammability UL 94V-2

Operating Temperature Max. continuous: 75°C; Min. continuous: -40°C without

impact





Online Resources

Customer Use Drawing eCatalog

Installation Instructions

