

Switches, Single Pole

20A, 120-277V AC

EdgeConnect™ Specification Grade Decorator Switch



Features

- Back wired screwless termination for faster termination time
- No need for screwdriver and torque wrench
- Spring Termination eliminates strand relaxation
- Strip gauge for accurate wiring
- Automatic self-grounding staple

Ordering Information

Description	Color	UPC	Catalog Number
Single Pole, Decorator	Gray	78358596450	DS120STGY

Listings

UL Listed  
CSA Certified  
Fed Spec

Specifications

Material	Polycarbonate
Contacts	Silver Alloy
Mounting Bridge	Galvanized Steel

Performance

<b>Electrical</b>	
Dielectric Voltage	Withstands 1500V AC minimum for 1 minute
Max. Continuous Current	20A
Max. Working Voltage	277V AC
Overload	Minimum 4.8 times rated current for 100 cycles
Temperature Rise	30°C maximum at rated current

<b>Mechanical</b>	
Terminal Accommodations	#14 AWG min. - #10 AWG max. solid and stranded copper wire only

<b>Environmental</b>	
Flammability	UL 94V-2
Operating Temperature	Max. continuous: 75°C; Min. continuous: -40°C without impact



Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

