Switches, Three Way 20A, 120-277V AC

Style Line® Decorator Series Specification Grade Switch

HUBBELL

Features

- Thread cleaning captive mounting screw
- Steel, zinc plated bridge is corrosion resistant
- Automatic self-grounding staple

Ordering Information

Description Rocker Color UPC Catalog Number Rocker, back and side Brown 783585151410 DS320 wired

Listings

UL Listed CSA Certified

Specifications

Rocker Material Thermoplastic
Contacts Silver Alloy
Terminal Screws Brass

Mounting Bridge Nickel Plated Steel with Auto Ground Staple

Contacts Silver Alloy Ground Screw Brass (Green)

Performance

Electrical

Dielectric Voltage Withstands 1500V AC minimum for 1 minute

Max. Continuous Current 20A Max. Working Voltage 277V AC

Overload Minimum 4.8 times rated current for 100 cycles

Temperature Rise 30°C maximum at rated current

Mechanical

Terminal Accommodations #14 AWG min. - #10 AWG max. solid and stranded copper

wire only


Environmental

Flammability UL 94V-2

Operating Temperature Max. continuous: 75°C; Min. continuous: -40°C without

impact





Online Resources

Customer Use Drawing

eCatalog

Installation Instructions

