

Floor Boxes

Flush Rectangular Concrete Floorboxes

3-Gang/ Multiservice

Features

- Typically used in 2nd Floor and Above Concrete Floors
- Pregalvanized Stamped Steel Box
- (16) 1/2", 3/4" and (6) 3/4", 1", 1-1/4" Concentric Knockouts
- 2.75" minimum depth of pour
- 1.25" prepour and 0.50" post pour adjustment

Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Rectangular	Above Grade	783585695945	FB2423

Listings

cULus Listed
UL 514A Listed
CSA C22.2 No 18 certificated

Specifications

Box Base Material	Stamped Steel
Box Top Material	Stamped Steel
Box Finish	Green Powder Paint
Concrete Cover	Tin Plate
Cover Frame Material	Thermoplastic
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Low Voltage Divider	Stamped Steel
Wiring Chamber Volumes	34.0 IN ³ [557.2 CM ³]; 35.0 IN ³ [573.5 CM ³] center gang

Performance

Mechanical

Box Height	2.75" [69.8mm]
Box Length	4.81" [122.2mm]
Box Width	12.50" [317.5mm]
Concrete Pour- Minimum Depth	2.75" [69.9mm]
Concrete Pour- Post Pour Adjustment	.50" [12.7mm]
Knockouts – Bottom	(6) 3/4", 1", 1-1/4"
Knockouts – Ends	(4) 1/2", 3/4"
Knockouts – Sides	(12) 1/2", 3/4"

HUBBELL



Related Products

Brass Cover Flange	S5017GR
Aluminum Cover Flange	SA5017GR
Brass Surface Flange	SB3085W
Aluminum Surface Flange	SA3085W

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

