

## Floor Boxes

### Flush Rectangular Concrete Floorboxes

#### 1-Gang/ Single Service

# HUBBELL

#### Features

- Typically used in 2nd Floor and Above Concrete Floors
- Pregalvanized Stamped Steel Box
- (6) 3/4", 1", 1-1/4" Concentric Knockouts
- 3.75" minimum depth of pour
- 1.25" prepour and 0.50" post pour adjustment

#### Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Rectangular	Above Grade	783585695952	FB2431

#### Listings

cULus Listed  
UL 514A Listed  
CSA C22.2 No 18 certificated

#### Specifications

Box Base Material	Cast Iron
Box Top Material	Stamped Steel
Box Finish	Green Powder Paint
Concrete Cover	Tin Plate
Cover Frame Material	Thermoplastic
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Low Voltage Dividers	Stamped Steel
Wiring Chamber Volumes	54.0 IN <sup>3</sup> [884.9 CM <sup>3</sup> ]

#### Performance

##### Mechanical

Box Height	3.73" [94.7mm]
Box Length	4.81" [122.2mm]
Box Width	6.00" [152.4mm]
Concrete Pour- Minimum Depth	3.75" [95.3mm]
Concrete Pour- Post Pour Adjustment	.50" [12.7mm]
Knockouts – Bottom	(2) 3/4", 1", 1-1/4"
Knockouts – Ends	(2) 3/4", 1", 1-1/4"
Knockouts – Sides	(2) 3/4", 1", 1-1/4"



#### Related Products

Brass Cover Flange	S5017GR
Aluminum Cover Flange	SA5017GR
Brass Surface Flange	SB3083W
Aluminum Surface Flange	SA3083W

#### Online Resources

Customer Sales Drawings  
eCatalog  
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

