

Floor Boxes

Flush Round Concrete Floorboxes

1-Gang/ Single Service

HUBBELL

Features

- Typically used in 2nd Floor and Above Concrete Floors
- Pregalvanized Stamped Steel Box
- (1) 1/2" & (1) 3/4", (2) 1/2" & (1) 3/4", (2) 3/4", 1", 1-1/4" Concentric Knockouts
- 3.00" minimum depth of pour
- 1.25" prepour and 0.50" post pour adjustment

Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Round	Above Grade	783585695990	FB2529

Listings

cULus Listed
UL 514A Listed
CSA C22.2 No 18 certificated

Specifications

Box Base Material	Stamped Steel
Box Top Material	Stamped Steel
Box Finish	Green Powder Paint
Concrete Cover	Tin Plate
Cover Frame Material	Thermoplastic
Device Chamber Grounding	6" Long #12 AWG Solid Copper Wire
Low Voltage Divider	NA
Wiring Chamber Volumes	37.3 IN ³ [611.2 CM ³]

Performance

Mechanical	
Box Height	2.82" [71.5mm]
Box Length	6.00" [152.4mm]
Box Width	4.81" [122.2mm]
Concrete Pour- Minimum Depth	3.00" [76.2mm]
Concrete Pour- Post Pour Adjustment	.50" [12.7mm]
Knockouts – Bottom	(2) 3/4", 1", 1-1/4"
Knockouts – Ends	(1) 1/2" & (1) 3/4"
Knockouts – Sides	(2) 1/2" & (1) 3/4"



Related Products

Brass Cover Flange	S5016
Aluminum Cover Flange	SA5016
Brass Carpet Flange	S3082
Aluminum Carpet Flange	SA3082

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

